

Rittal – The System.

Faster – better – everywhere.



KEL 9409.600 Ex enclosures

State: 31/01/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9409.600 - Ex enclosures Stainless steel, empty enclosure with hinged door

Ex enclosure with hinged door, stainless steel

Features

Model No.	KEL 9409.600
Design	Ex enclosures
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure Door Mounting plate
Dimensions	Width: 300 mm Height: 380 mm Depth: 210 mm
Dimensions mounting plate (W x H)	275 mm x 334 mm
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit
IP protection category to IEC 60529	IP 66
Protection category NEMA	NEMA 4X

Features

Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12
-----------------------	--

Packs of	1 pc(s).
----------	----------

Net weight	7.88
------------	------

Gross weight	8.12
--------------	------

Customs tariff number	94032080
-----------------------	----------

EAN	4028177138926
-----	---------------

ETIM 9	EC002503
--------	----------

ECLASS 8.0	27180502
------------	----------

Approvals

Approvals	ATEX CQC-CCC IEC Ex UL + C-UL (listed)
-----------	---