

# Rittal – The System.

Faster – better – everywhere.



## PK 9519.000

# Polycarbonate enclosures PK

State: 03/01/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9519.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | PK 9519.000   |
| Design                            | PK enclosure with solid cover   |
| Product description               | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.  |
| Material                          | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour                            | RAL 7035  |
| Supply includes                   | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |
| Dimensions                        | Width: 182 mm<br>Height: 180 mm<br>Depth: 165 mm  |
| Operating temperature range       | -35 °C...80 °C  |
| Basic material                    | Polycarbonate   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0.841   |

# Features

---

|                       |               |
|-----------------------|---------------|
| Gross weight          | 0.941         |
| Customs tariff number | 94037000      |
| EAN                   | 4028177139695 |
| E-Number Sweden       | E3404592      |
| ETIM 9                | EC000261      |
| ECLASS 8.0            | 27180101      |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | C-UL<br>DNV-GL<br>UL      |
| Explanations | Declaration of conformity |

---