


# Rittal – The System.

Faster – better – everywhere.



## SV 9635.025 Board

State: 17/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.025 - Board RiLine Compact

Board with integral busbars.

## Features

Model No.	SV 9635.025
Function principle	Shock-hazard-protected busbar board for the safe accommodation and contacting of components, thanks to simple plug-in mounting Pre-punched pitch units in the board allow secure, fast positioning of components Reduces wiring work by contacting directly onto the board
Material	Polyamide Polycarbonate E-Cu Fire protection corresponding to UL 94
Colour	RAL 7035
Supply includes	Integral busbars
Supply includes	Integral busbars
IP protection category to IEC 60529	IP 20
Standards	UL 508 IEC 61 439
Rated current max.	160 A
Rated operating voltage	690 V (AC) 600 V (DC)
Note	The technical data may vary for UL applications
for mounting plate assembly	Yes
Dimensions	Width: 600 mm Height: 160 mm Depth: 45.1 mm
Packs of	1 pc(s).
Copper weight (kg per piece)	1.34

# Features

---

Customs tariff number	85469010
EAN	4028177978430
ETIM 8	EC001900
ETIM 7.0	EC001900
ECLASS 8.0	27400613

---

# Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------

---