

Rittal – The System.

Faster – better – everywhere.



SK 3184.800

Blue e+ S wall-mounted cooling unit

State: 16.07.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3184.800 - Blue e+ S wall-mounted cooling unit 0.3 kW – 1 kW

Blue e+ S cooling units with tried-and-tested Blue e+ technology are the world's most energy-efficient cooling units. This means they reduce the carbon footprint of your machines and systems. Available in a brand new design with a host of smart functions.



Features

| | |
|-----------------|---|
| Model No. | SK 3184.800 |
| Design | Integral electric condensate evaporation |
| Benefits | Contributes to climate-neutral production with average energy savings of 75% and a reduced carbon footprint The use of R-513A refrigerant makes them more environmentally friendly Multi-voltage capabilities and country-specific approvals support global usability Smart, simple monitoring via IoT interface User-friendly operation with the Rittal Scan & Service app |
| Material | Sheet steel |
| Colour | Enclosure: RAL 7035 Louvred grille: RAL 7012 |
| Supply includes | Assembly parts Fully wired ready for connection (plug-in terminal strip) Integral electric condensate evaporation |
| Options | For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages. |

Features

| | |
|--|--|
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 1 kW Cooling output L35 L35/60 Hz: 1 kW Cooling output L35 L50/50 Hz: 0.6 kW Cooling output L35 L50/60 Hz: 0.6 kW |
| Rated operating voltage | 110 V - 240 V, 1~, 50 Hz/60 Hz |
| Note | Please observe the mounting instructions. By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions. Only suitable for use in semi-outdoor areas (see instructions for description) |
| Note on Model No. | Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V) |
| Rated power input | 0,6 kW |
| Air throughput (unimpeded air flow) | External circuit: 680 m ³ /h Internal circuit: 680 m ³ /h |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.4 Refrigeration factor L35 L35 (EER) 60 Hz: 2.4 |
| Design | wall-mounted |
| Dimensions | Width: 400 mm Height: 950 mm Depth: 196 mm |
| Required mounting cut-out | Cut-out width: 383 mm Cut-out height: 929 mm |
| Protection category to IEC 60 529 | Internal circuit IP 55 |
| Protection category NEMA | UL Type 3R/12 |
| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 0.31 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.2 t |
| Temperature control | e+ controller (factory setting +35 °C) |
| Operating temperature range | -20 °C...60 °C |
| Storage temperature range | -40 °C...70 °C |

Features

| | |
|---|--|
| Operating temperature range of refrigerant circuit (active) | 3 °C...60 °C |
| Heat pipe operating temperature range | -20 °C...45 °C |
| Setting range | 20 °C...50 °C |
| Power consumption Pel | Power consumption L35 L35/50 Hz: 0.42 kW Power consumption L35 L35/60 Hz: 0.42 kW Power consumption L35 L50/50 Hz: 0.48 kW Power consumption L35 L50/60 Hz: 0.48 kW |
| Permissible operating pressure (p. max.) | 34 bar |
| Packs of | 1 pc(s). |
| Weight/pack | 26,2 kg |
| Customs tariff number | 84158200 |
| EAN | 4028177949973 |
| ETIM 8 | EC000855 |
| ETIM 7.0 | EC000855 |
| ECLASS 8.0 | 27180704 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) UL + C-UL - FTFA |
| Explanations | Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK |
