


Rittal – The System.

Faster – better – everywhere.



SV 3562.000 Plate clamp

State: 27.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3562.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

Model No.	SV 3562.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	54 x 10 mm
To fit busbars	50 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Weight/pack	1,413 kg
Net weight	1.2
Gross weight	1.412
PCF/PU (Cradle-to-Gate)	5.4 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	85369010
EAN	4028177044395
ETIM 8	EC000001
ETIM 7.0	EC000001
ECLASS 8.0	27141146

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SV plate clamps

for E-Cu busbars with 3 - 10 mm thickness.

For bar width: up to 50 mm

Clamping area for laminated copper bars:

54 x 10 mm

Tightening torque:

6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated