


Rittal – The System.

Faster – better – everywhere.



VX 8640.003

**Base/plinth corner piece with base/
plinth trim panels, front and rear,
100 mm**

State: 27.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.003 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.

Features

| | |
|---------------------|---|
| Model No. | VX 8640.003 |
| Product description | High-load capacity base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover. |
| Material | Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic |
| Colour | RAL 9005 |
| Supply includes | 4 base/plinth corner pieces, 100 mm high 4 corner covers 1 baying cover 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts |
| Note | Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth |
| Dimensions | Height: 100 mm |

Features

| | |
|--------|---|
| To fit | Enclosure type: VX VX IT VX SE TE TS TS IT TX CableNet Width: = 800 mm |
|--------|---|

| | |
|-----------------------|-------------------|
| Type rating to UL 50E | Type 1 Type 12 |
|-----------------------|-------------------|

| | |
|-------------|---------|
| Weight/pack | 5,18 kg |
|-------------|---------|

| | |
|----------|----------|
| Packs of | 2 pc(s). |
|----------|----------|

| | |
|------------|-----|
| Net weight | 4.4 |
|------------|-----|

| | |
|--------------|------|
| Gross weight | 5.68 |
|--------------|------|

| | |
|-----------------------|----------|
| Customs tariff number | 94039910 |
|-----------------------|----------|

| | |
|-----|---------------|
| EAN | 4028177958753 |
|-----|---------------|

| | |
|-----------------|----------|
| E-Number Sweden | E3465364 |
|-----------------|----------|

| | |
|--------|----------|
| ETIM 8 | EC000721 |
|--------|----------|

| | |
|----------|----------|
| ETIM 7.0 | EC000721 |
|----------|----------|

| | |
|------------|----------|
| ECLASS 8.0 | 27182003 |
|------------|----------|

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|