

Rittal – The System.

Faster – better – everywhere.



SV 9343.010

NH fuse-switch-disconnectors, size 00 to 3

State: 27.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.010 - NH fuse-switch-disconnectors, size 00 to 3

Features

Model No.	SV 9343.010
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 20 mm Clamping area height: 5 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
For NH size	00
Note	The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses".
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection for round conductor cross-sections	10 - 95 mm ²
To fit busbars	Height: 5, 10 mm
Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).

Features

Weight/pack	0,94 kg
Net weight	0.84
Gross weight	0.94
Copper weight (kg per piece)	0.2
Customs tariff number	85369095
EAN	4028177540262
ETIM 7.0	EC001040
ECLASS 8.0	27371401

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK