

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.350

# NH fuse-switch-disconnectors, size 00 to 3

State: 19.10.2024. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.350 - NH fuse-switch-disconnectors, size 00 to 3 with electromechanical fuse monitoring

## Features

Model No.	SV 9343.350
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	630 A
For NH size	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm
Connection for round conductor cross-sections	10 - 300 mm <sup>2</sup>
To fit busbars	Height: 5, 10 mm
Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	4,58 kg

# Features

---

Net weight	4.5
Gross weight	4.705
Copper weight (kg per piece)	1.44
Customs tariff number	85369095
EAN	4028177540491
ETIM 7.0	EC001040
ECLASS 8.0	27371401

# Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK