


# Rittal – The System.

Faster – better – everywhere.



## SV 9635.010 Board

State: 19.10.2024. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.010 - Board RiLine Compact

Board with integral busbars.

## Features

Model No.	SV 9635.010
Function principle	Shock-hazard-protected busbar board for the safe accommodation and contacting of components, thanks to simple plug-in mounting Pre-punched pitch units in the board allow secure, fast positioning of components Reduces wiring work by contacting directly onto the board
Material	Polyamide Polycarbonate E-Cu Fire protection corresponding to UL 94
Colour	RAL 7035
Supply includes	Integral busbars
Supply includes	Integral busbars
IP protection category to IEC 60529	IP 20
Standards	UL 508 IEC 61 439
Rated current max.	125 A
Rated current (UL)	100 A
Rated operating voltage	690 V (AC) 600 V (DC)
Rated operating voltage (max.) UL	600 V (AC) 600 V (DC)
Max. pitch units @ 45 mm	9
Note	The technical data may vary for UL applications
For mounting on support rails	Yes

# Features

---

for mounting plate assembly	Yes
Dimensions	Width: 405 mm Height: 160 mm Depth: 45.1 mm
Packs of	1 pc(s).
Weight/pack	1,377 kg
Net weight	1.3
Gross weight	1.46
Copper weight (kg per piece)	0.551
Customs tariff number	85469010
EAN	4028177817401
ETIM 8	EC001900
ETIM 7.0	EC001900
ECLASS 8.0	27400613

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK