

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.700 Component adaptor

State: 27.09.2024. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.700 - Component adaptor clamping attachment

For circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. For bar systems with 185 mm centre-to-centre spacing.

## Features

|   |  |
|---|--|
| Model No.                                     | SV 9677.700  |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Colour  | RAL 7035   |
| For bar systems with centre-to-centre spacing | 185 mm   |
| Cable outlet                                  | Bottom   |
| Installation type                             | Clamping attachment  |
| Number of poles                               | 3-pole   |
| Rated current max.                            | 1.000 A  |
| Rated operating voltage                       | 690 V, 3~  |
| Note  | Cable outlet: Switch outlet or as outgoing cable from the switchgear<br>Suitable for the use of switchgear with front screw terminal<br>For mounting on busbar systems with or without cover section |
| Dimensions                                    | Width: 300 mm<br>Height: 652 mm  |
| To fit busbars                                | Height: 10 mm  |
| To fit manufacturer (model)                   | ABB (Tmax T7 - 800 A/1000 A)<br>Eaton (NZM4 - 800 A/1000 A)<br>Schneider Electric (NS - 800 A/1000 A)<br>Siemens (VL1250/3VL7 - 1000 A)  |
| Packs of                                      | 1 pc(s).   |
| Weight/pack                                   | 15,3 kg  |
| Net weight                                    | 13.3   |

# Features

---

|                              |               |
|------------------------------|---------------|
| Gross weight                 | 15.28         |
| Copper weight (kg per piece) | 7.745         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177707092 |
| ETIM 7.0                     | EC001531      |
| ECLASS 8.0                   | 27370304      |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |