

Rittal – The System.

Faster – better – everywhere.



SV 9340.730 OM adaptors

State: 12/03/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.730 - OM adaptors with connection cables



Features

Model No.	SV 9340.730
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Connection cables (AWG)	AWG 8
Rated current max.	40 A
Rated operating voltage	690 V, 3~
Electrical ratings UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7 65 kA - 480 V, Manual Motor Controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	130 mm
Support rail type	TS 55D TS 55D-V
Note	The technical data may vary for UL applications
Number of poles	3-pole
Support frame support	Yes

Features

Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Packs of	1 pc(s).
Net weight	0.36
Gross weight	0.382
Copper weight (kg per piece)	0.088
Customs tariff number	85369095
EAN	4028177664258
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK