

# Rittal – The System.

Faster – better – everywhere.



## SK 7980.000 Fan expansion kit

State: 19.10.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 7980.000 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

## Features

Model No.	SK 7980.000
Product description	For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate.
Supply includes	Fan Connection cable (0.61 m) Assembly parts
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 160 m <sup>3</sup> /h At 60 Hz: 180 m <sup>3</sup> /h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 15 W At 60 Hz: 14 W
Dimensions	Width: 119 mm Height: 119 mm Depth: 38 mm
Operating temperature range	-10 °C...55 °C
Noise level	At 50 Hz: 37 dB(A) At 60 Hz: 37 dB(A)
Weight/pack	0,67 kg
Packs of	1 pc(s).
Net weight	0.6
Gross weight	0.671
Customs tariff number	84149000
EAN	4028177137752
ETIM 7.0	EC000320
ECLASS 8.0	27180716

# Tender text

Fan expansion kit for fan mounting plate

Rated operating voltage: 230V; Power consumption: 19/18

W at 50/60 Hz;

Air throughput (unimpeded air flow): 160 - 180 m<sup>3</sup>/h at  
50/60 Hz;

Temperature range: -10°C to +55°C

Dimensions (W x H x D): 119 mm x 119 mm x 38 mm