


**Rittal – The System.**

Faster – better – everywhere.



# VX 8619.410

## Cable clamp rail

State: 27.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.410 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

## Features

Model No.	VX 8619.410
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure width 600 mm, in the base
VX SE installation options	In enclosure width 600 mm, in the base
AX installation options	In enclosure width 600 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
PC installation options	In enclosure width 600 mm, in the base
WI installation options	In enclosure width 600 mm, in the base
To fit	Base/plinth system AX Base/plinth system VX Base/plinth system VX, stainless steel
Dimensions	Length: 554 mm
To fit	Enclosure type: VX VX SE PC IW AX CX pedestal null Width: = 600 mm

# Features

Packs of	2 pc(s).
Weight/pack	3,24 kg
Net weight	3.2
Gross weight	3.395
Customs tariff number	73269098
EAN	4028177921931
ETIM 7.0	EC000322
ECLASS 8.0	27400604