

Rittal – The System.

Faster – better – everywhere.



SV 9340.530 OM adaptors

State: 19.10.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.530 - OM adaptors with spring terminals



Features

Model No.	SV 9340.530
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	TS 45C
Number of poles	3-pole
Dimensions	Width: 45 mm Height: 208 mm
Connection for round conductor cross-sections	1.5 - 6 mm ²
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm
Packs of	1 pc(s).
Weight/pack	0,26 kg

Features

Net weight	0.259
Gross weight	0.28
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177502628
ETIM 7.0	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 32 A
OM adaptor 32 A with tension spring clamp, 3-pole,
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Construction width: 45 mm
Length: 208 mm
Support frame: 45 x 170 mm
Support frame support: -
PinBlock: -
Connector outlet: -
Support rail: 1 with anti-slip guard
System:
Rittal RiLine60