

Rittal – The System.

Faster – better – everywhere.



SV 9340.860 Cable set

State: 26.09.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.860 - Cable set for OM adaptors with spring terminal block

Pre-assembled connection cables for individual connection of switchgear.



Features

Model No.	SV 9340.860
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 12 = 3.31 mm ² ∅ 4 mm ²
Length	140 mm
Note	AWG = American Wire Gauge
Dimensions	Length: 140 mm
Packs of	15 pc(s).
Weight/pack	0,09 kg
Net weight	0.075
Gross weight	0.085
Copper weight (kg per piece)	0.003
Customs tariff number	85444290
EAN	4028177502710

Features

ETIM 7.0	EC000839
ECLASS 8.0	27062302

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK