

Rittal – The System.

Faster – better – everywhere.



SV 9343.040

NH fuse-switch-disconnectors, size 00 to 3

State: 27.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.040 - NH fuse-switch-disconnectors, size 00 to 3 with electromechanical fuse monitoring

Features

Model No.	SV 9343.040
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 13 mm Clamping area height: 13 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated operating current max.	160 A
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection for round conductor cross-sections	4 - 95 mm ²
To fit busbars	Height: 5, 10 mm
Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	1,06 kg

Features

Net weight	1.2
Gross weight	1.311
Copper weight (kg per piece)	0.2
Customs tariff number	85369095
EAN	4028177540309
ETIM 7.0	EC001040
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK