

Rittal – The System.

Faster – better – everywhere.



SV 9344.250

NH fuse-switch-disconnectors, size 00 to 3

State: 27.09.2024. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.250 - NH fuse-switch-disconnectors, size 00 to 3 with electromechanical fuse monitoring

Features

Model No.	SV 9344.250
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	400 A
For NH size	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm
Connection for round conductor cross-sections	10 - 240 mm ²
Rated operating voltage	690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	4,04 kg
Net weight	3.4

Features

Gross weight	3.481
Copper weight (kg per piece)	1
Customs tariff number	85369095
EAN	4028177540712
ETIM 7.0	EC001040
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK