

Rittal – The System.

Faster – better – everywhere.



DK 9788.173 PS Server Enclosures

State: 26/9/2024 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 9788.173 - PS Server Enclosures

Rittals rugged PS networking enclosures are an ideal solution for network applications. The PS server enclosure is one of the most cost effective and versatile solutions in the market today.



Features

Model No.	DK 9788.173
Product description	Rittals rugged PS networking enclosures are an ideal solution for network applications. The PS server enclosure is one of the most cost effective and versatile solutions in the market today.
Benefits	Frames are bayable, scalable and modular Static load capacity of 1.000 kg on 19" mounting angles (total load of 1.400 kg on enclosure frame) Comply to EIA 310 and IEC 297 standards
Material	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Base: sheet steel, 1.5 mm Mounting angles: sheet steel, 2 mm
Surface finish	dipcoat-primed and powder-coated, textured paint Mounting angles: Zinc-plated
Colour	RAL 9005
Supply includes	Enclosure frame Roof plate with cable entry Base plate with cable entry 482.6 mm (19") level, L-shaped mounting angles on punched sections with mounting flanges, front and rear, depth-variable
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,200 mm

Features

Packs of	1 pc(s).
Net weight	0.01
Gross weight	0.01
