

Rittal – The System.

Faster – better – everywhere.



HD 4000.062 Command panel HD

State: 2024.9.27 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.062 - Command panel HD

Monitors, PCs and other components with displays are hygienically and securely protected in the command panel. The roof tilt of 30° prevents objects from being deposited on it, and allows liquids to run off quickly.

Features

| | |
|--------------------------------|---|
| Model No. | HD 4000.062 |
| Benefits | Roof angled forwards by 30° Height-adjustable mounting plate for screen up to 24" Holder for desktop TFT, height-adjustable for screens up to 24" |
| Material | Enclosure and door: Stainless steel 1.4301 (AISI 304) Lock insert HD: Stainless steel 1.4404 (AISI 316L) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate |
| Surface finish | Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010) |
| Supply includes | Enclosure of all-round solid construction Door with viewing window and inserted seal R/h door hinge Holder for desktop TFT with VESA 75/100 locator |
| Options | without viewing window Mounting panel instead of a mounting plate Cut-out for touch panel instead of viewing window HD keyboard support |
| Dimensions | Width: 810 mm Height, front: 692 mm Height rear: 848 mm Depth: 266 mm |
| Visible area | Viewing window width: 535 mm Viewing window height: 325 mm |
| Material thickness - enclosure | 1.5 mm |

Features

| | |
|-----------------------------------|----------------|
| Material thickness - door | 2 mm |
| Protection category to IEC 60 529 | IP 66 IP X9 |
| Protection category NEMA | NEMA 4X |
| IK Code | IK08 |
| Packs of | 1 pc(s). |
| Weight/pack | 33.2 kg |
| Net weight | 33.2 |
| Gross weight | 33.2 |
| Customs tariff number | 94032080 |
| EAN | 4028177709539 |
| ETIM 8 | EC000261 |
| ETIM 7.0 | EC000261 |
| ECLASS 8.0 | 27180101 |