

Rittal – The System.

Faster – better – everywhere.



AS 4055.137

Splitter hole punch, round

State: 2024.10.19 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.137 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.137
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Maximum machinable material thickness, stainless steel	2.5 mm
Ø punch	37 mm
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Weight/pack	0.311 kg
Net weight	0.311
Gross weight	0.343
Customs tariff number	82073010
EAN	4028177808072
ETIM 8	EC000156
ETIM 7.0	EC000156

Features

ECLASS 8.0

21049047