


Rittal – The System.

Faster – better – everywhere.



VX 8660.005

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 2024.7.13 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.005 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces for flexible cable entry options plus a positioning aid for simple enclosure mounting on the base/plinth.

Features

Model No.	VX 8660.005
Benefits	Reliable – Excellent stability of the base/plinth Flexible – Countless interior installation options with VX accessories Simple – Flush termination between the baying points
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 corner covers Assembly parts 4 base/plinth corner pieces, 100 mm high 2 base/plinth trim panels, front/rear, 100 mm high
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth
Dimensions	Height: 100 mm

Features

To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 1,000 mm
--------	---

Type rating to UL 50E	Type 1 Type 12
-----------------------	-------------------

Weight/pack	6.19 kg
-------------	---------

Packs of	2 pc(s).
----------	----------

Customs tariff number	94039910
-----------------------	----------

EAN	4028177978089
-----	---------------

ETIM 8	EC000721
--------	----------

ETIM 7.0	EC000721
----------	----------

ECLASS 8.0	27182003
------------	----------
