

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.100

# NH fuse-switch-disconnectors, size 00 to 3

State: 1/2/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.100 - NH fuse-switch-disconnectors, size 00 to 3

## Features

Model No.	SV 9343.100
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 20 mm Clamping area height: 3 mm
Note	Connection of sector-shaped conductors 50 – 150 mm <sup>2</sup> .
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated operating current max.	250 A
Rated operating voltage	690 V, 3~
For NH size	1
Note	The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses".
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm
Connection for round conductor	35 - 150 mm <sup>2</sup>
To fit busbars	Height: 5, 10 mm
Clamping area for laminated copper bars	14 mm

# Features

---

Number of poles	3-pole
Packs of	1 pc(s).
Net weight	2.1
Gross weight	2.378
Copper weight (kg per piece)	0.44
Customs tariff number	85369095
EAN	4028177540323
ETIM 9	EC001040
ECLASS 8.0	27371401

# Approvals

---

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK