

**Rittal – The System.**

Faster – better – everywhere.



**PK 9524.100**

**Polycarbonate enclosures PK**

State: 2024.10.19 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9524.100 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | PK 9524.100  |
| Design                            | null   |
| Product description               | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.   |
| Material                          | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover transparent: Polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour                            | RAL 7035   |
| Supply includes                   | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws  |
| Protection category NEMA          | NEMA 4X  |
| Protection category to IEC 60 529 | IP 66  |
| IK Code                           | IK08   |
| Dimensions                        | Width: 360 mm<br>Height: 254 mm<br>Depth: 165 mm   |
| Operating temperature range       | -35 °C...80 °C   |
| Basic material                    | Polycarbonate  |
| Packs of                          | 1 pc(s).   |
| Weight/pack                       | 1.92 kg  |
| Net weight                        | 1.72   |

# Features

---

|                       |               |
|-----------------------|---------------|
| Gross weight          | 1.92          |
| Customs tariff number | 94037000      |
| EAN                   | 4028177139916 |
| ETIM 7.0              | EC000261      |
| ECLASS 8.0            | 27180101      |

---

# Approvals

---

|           |                      |
|-----------|----------------------|
| Approvals | C-UL<br>DNV-GL<br>UL |
|-----------|----------------------|

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

---