

Rittal – The System.

Faster – better – everywhere.



DK 5502.205 Rangerpanel

State: 2024-09-27 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.205 - Rangerpanel med stålbyglar

För horisontell rangering av kontaktdonskabeln med 5 kabelföringsöglor.

Features

Art. nr.	DK 5502.205
Produktbeskrivning	För horisontell rangering av kontaktdonskabeln med 5 kabelföringsöglor.
Material	Panel: Stålblåt Bygel: Stål
Ytbehandling	Panel: lackerad Bygel: Förzinkad
Färg	RAL 9005
Observera:	Måtten avser yttermått.
Dimension	Bredd: 482,6 mm
Höjdenheter	1 HE
Bygelmått	Ring depth: 55 mm Ring height: 43 mm
Förpackningsenhet	1 st.
Vikt/förp.	0,763 kg
Nettovikt	0.57
Bruttovikt	0.599
PCF/PU (Cradle-to-Gate)	2,9 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Tullvarukod	94039910
EAN	4028177679320
E-Number Sweden	E7239783
ETIM 7.0	EC000322

Features

ECLASS 8.0

27400604