

# Rittal – The System.

Faster – better – everywhere.



## CS 9765.082

## Concrete base/plinth

State: 27/09/2024 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9765.082 - Concrete base/plinth for outdoor enclosures

Concrete base/plinth for CS Toptec and basic enclosures. The base/plinth is made from pre-cast concrete sections which are easily fitted in situ.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | CS 9765.082   |
| Product description   | The base/plinth is made from pre-cast concrete sections which are easily fitted in situ. Front/rear base/plinth plate screw-fastened from the inside, removable for servicing access. |
| Material              | Light-weight concrete   |
| Surface finish        | Untreated   |
| Supply includes       | 1 base plate<br>2 side parts<br>2 divided base/plinth plates<br>Assembly parts and fastening screws for mounting the enclosure.   |
| Excavation depth      | 700 mm  |
| Note                  | Extended delivery times.  |
| Note on Model No.     | Extended delivery times.  |
| Dimensions            | Height: 965 mm  |
| To fit                | Enclosure type: CS basic enclosures<br>Width: 600 mm<br>Depth: 500 mm   |
| Suitable for depth    | 500 mm  |
| Packs of              | 1 pc(s).  |
| Weight/pack           | 215 kg  |
| Net weight            | 200   |
| Gross weight          | 201   |
| Customs tariff number | 68109100  |

# Features

---

|            |               |
|------------|---------------|
| EAN        | 4028177216761 |
| ETIM 7.0   | EC000721      |
| ECLASS 8.0 | 27182003      |

---

## Tender text

Concrete base/plinth for outdoor enclosures

Base made from ready-mixed concrete slabs, prepared for outdoor enclosures with basic W x D dimensions of 600 x 500 mm. The excavation depth for a 1000 mm high base is approx. 700 mm.

Material: Light concrete

For enclosures: W x D: 600 x 500 mm