


# Rittal – The System.

Faster – better – everywhere.



## TE 7888.940 Distributor racks

State: 26/04/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.940 - Distributor racks TE 8000 open

For optimum accessibility from all sides during assembly and installation.

## Features

|   |  |
|---|--|
| Model No.   | TE 7888.940  |
| Benefits  | Optimum accessibility from all sides during assembly and installation<br>Unrestricted airflow, due to the open design<br>The distance between attachment levels is infinitely variable   |
| Material  | Sheet steel  |
| Surface finish  | Powder-coated  |
| General colour  | RAL 7035   |
| Colour  | RAL 7035   |
| Supply includes   | Self-supporting mounting frame, with 482.6 mm (19") mounting level front and rear<br>Roof-plate, prepared for accommodating cable organisers<br>Open base frame with 2 punched sections with mounting flanges for individual configuration fitted in the width<br>4 levelling feet, M10 (supplied loose)<br>Roof plate with brush strip, rear horizontal |
| Dimensions  | Width: 600 mm<br>Height: 2,000 mm<br>Depth: 1,000 mm   |
| Units   | 42 U   |
| Units   | 42 U   |
| Free mounting space to the 482.6 mm (19") level, front/rear | 80 mm / 130 mm   |
| Distance between levels as delivered                        | 745 mm   |
| Load capacity   | 7.000 N  |
| Basic material  | Sheet steel  |

# Features

|                 |               |
|-----------------|---------------|
| Packs of        | 1 pc(s).      |
| Net weight      | 33            |
| Gross weight    | 35            |
| EAN             | 4028177801554 |
| E-Number Sweden | E7282509      |
| ETIM 9          | EC002507      |
| ECLASS 8.0      | 27180602      |

# Tender text

TE 8000 network distributor, open frame  
Item TE 7888.940

Screw-fastened, dismountable enclosure design based on two self-supporting 482.6 mm (19") mounting angles, which simultaneously form the supporting distributor frame. Roof and modular base frames connected together using 482.6 mm (19") mounting frames to form a supporting frame. Open distributor frame, without side panels and doors. Open roof frame for cable entry including three cable routing trays. Base frame with maximum cut-out for optional population with modular panels, pre-configured, with 2 punched sections in the width for individual configuration. Two depth-adjustable 482.6 mm (19") mounting frames with integrated 25 mm system punching are used for the internal assembly. Mounting frames may be secured infinitely by means of slot attachment. 350 kg load capacity per frame, max. 700 kg for each distributor. The distributor frames are bayable.

Supply includes: Open frame with levelling feet to compensate for floor irregularities.

Material: Sheet steel

Surface finish: RAL 7035

Approvals: ---

Dimensions (WHD): 600 x 2000 x 1000 mm

Installation clearance height: 42 U

Protection category: ---

Model No: TE 7888.940

Manufacturer: Rittal GmbH & Co. KG