

Rittal – The System.

Faster – better – everywhere.



SK 3359.540

TopTherm Blue e roof-mounted cooling unit

State: 19.10.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3359.540 - TopTherm Blue e roof-mounted cooling unit

Total cooling output 0.50 - 4.00 kW

Energy-efficient Blue e roof-mounted cooling units in output categories from 500 W to 4,000 W with e-Comfort controller integrated as standard and electrical condensate evaporation.

Features

Model No.	SK 3359.540
Design	roof-mounted
Product description	Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard.
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.77 kW Cooling output L35 L35/60 Hz: 0.75 kW Cooling output L35 L50/50 Hz: 0.52 kW Cooling output L35 L50/60 Hz: 0.47 kW
Rated operating voltage	400 V, 2~, 50 Hz/60 Hz 400 V AC
Note	The roof-mounted cooling unit 3273.500 is also suitable for office applications, thanks to its low noise level.
Rated current max.	At 50 Hz: 1.6 A At 60 Hz: 2.1 A

Features

Start-up current max.	At 50 Hz: 5.4 A At 60 Hz: 5.2 A
Air throughput (unimpeded air flow)	External circuit: 800 m ³ /h Internal circuit: 585 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.14 Refrigeration factor L35 L35 (EER) 60 Hz: 1.79
Design	roof-mounted
Dimensions	Width: 597 mm Height: 417 mm Depth: 380 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.4 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.25 t
Type of electrical connection	Plug-in terminal strip
Duty cycle	100 %
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.36 kW Power consumption L35 L35/60 Hz: 0.42 kW Power consumption L35 L50/50 Hz: 0.49 kW Power consumption L35 L50/60 Hz: 0.48 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Transformer circuit-breaker: 6.3...10 A
Packs of	1 pc(s).
Weight/pack	37 kg

Features

Net weight	38.95
Gross weight	41
Customs tariff number	84158200
EAN	4028177433717
ETIM 8	EC000855
ETIM 7.0	EC000855
ECLASS 8.0	27180704

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
