

Rittal – The System.

Faster – better – everywhere.



SV 3560.000 Plate clamp

State: 26.9.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3560.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

| | |
|---|---|
| Model No. | SV 3560.000 |
| Product description | For connecting laminated copper bars, no drilling required. |
| Material | Sheet steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 34 x 10 mm |
| To fit busbars | 50 x 10 |
| To fit busbars | Busbar E-Cu |
| Packs of | 3 pc(s). |
| Weight/pack | 1,044 kg |
| Net weight | 0.999 |
| Gross weight | 1.043 |
| PCF/PU (Cradle-to-Gate) | 4 kg CO2 eq (Cat B) |
| Note on the PCF class | Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared |
| Customs tariff number | 85369010 |
| EAN | 4028177044357 |
| ETIM 8 | EC000001 |
| ETIM 7.0 | EC000001 |
| ECLASS 8.0 | 27141146 |

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SV plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For bar width: up to 50 mm

Clamping area for laminated copper bars:

34 x 10 mm

Tightening torque: 6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated