

Rittal – The System.

Faster – better – everywhere.



AS 4050.082 Busbar clammer

State: 19.10.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.082 - Busbar clumper

The simple solution for clamping copper bars/busbars on Perforex BC machining centres BC and Perforex milling terminals MT.



Features

Model No.	AS 4050.082
Design	Simultaneous clamping of three short copper bars (material thickness 5 or 10 mm)
Product description	Busbar clumper for Perforex machining centres BC and Perforex milling terminals MT, for simple machining of copper bars. Suitable for drilling and thread tapping.
Machinable length with 5 mm thickness	150 - 300 mm
Machinable height (max.)	30 - 120 mm
Machinable length with 10 mm thickness	150 - 1,000 mm
Simultan_Clamping of 3 copper bars	Yes
To fit Model No.	4050.101 4055.910 4055.911
Packs of	2 pc(s).
Weight/pack	12 kg
Customs tariff number	84669360

Features

EAN	4028177804517
ETIM 8	EC003010
ETIM 7.0	EC003010
ECLASS 8.0	36609190
