

Rittal – The System.

Faster – better – everywhere.



TX 7888.200

Network rack TX CableNet

State: 19.10.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TX 7888.200 - Network rack TX CableNet with glazed door

The TX CableNet – places extra space at your disposal by avoiding the problem of unnecessarily wide or deep IT racks. This IT network rack is thus also suitable for use in smaller IT environments and is already optimally prepared for individual interior installation.

Features

Model No.	TX 7888.200
Design	with glazed door
Benefits	Site-variable cable routing Safe cable entry whilst maintaining the critical cable bending radius "Waterfall" cable routing concept: Simple, safe cable routing via the roof Convenient access: Side panels and doors are easily fitted and removed for fast access to the inner rack area TS- and VX-compatible accessories Comprehensive range of accessories for bespoke interior configuration
Material	Enclosure: Sheet steel Door: Sheet steel, 1.2 mm Side panel: Sheet steel, 1.2 mm 482.6 mm (19") mounting angles: Sheet steel, 2 mm
Surface finish	Enclosure frame: Dipcoat-primed Enclosure panels: Dipcoat-primed, powder-coated
General colour	RAL 7035
Colour	RAL 7035

Features

Supply includes	Enclosure with glazed front door and rear door Side panels, screw fastened 482.6 mm (19") mounting angles Enclosure frame with doors and roof plate Glazed sheet steel front door, 180° hinges Sheet steel rear door, solid, one-piece, 130° hinges Fastener front and rear: Designer handle with security lock 3524 E Side panels, lockable, including security lock 3524 E Roof plate, welded, with waterfall concept for cable entry at the side, with a concealed cut-out for the fan module Two 482.6 mm (19") mounting angles, front and rear IPPC pallet
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 1,000 mm
Units	42 U
Units	42 U
Distance between levels as delivered	645 mm
Design	with side panels
Design doors	Glazed door, one-piece With 3 mm single-pane safety glass
Rear door design	Sheet steel rear door, solid, one-piece, 130° hinges
Front door design	Glazed sheet steel front door, 180° hinges
Load capacity	5000 N
Load capacity	5.000 N
Basic material	Sheet steel
Packs of	1 pc(s).
Weight/pack	152 kg
Net weight	139.175
Gross weight	146.5
Customs tariff number	94032080

Features

EAN	4028177963450
E-Number Sweden	E7238493
ETIM 8	EC002499
ETIM 7.0	EC002499
ECLASS 8.0	27180207

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

IT rack, installation height 42 U, glazed sheet steel door at the front, one-piece solid sheet steel door at the rear.

Rack frame:

IT rack, comprising a torsionally rigid, welded and symmetrical frame of rolled, 16-fold vertical sections connected with a horizontal frame at the bottom and horizontal cross rails with welded roof plate at the top.

All frame sections with integrated system punching in a 25 mm pitch pattern permit convenient interior installation through simple attaching and fastening of the installation components. All section edges are rounded. The vertical frame sections each possess two mounting levels offset in the depth and width directions, which can be used individually for flexible mounting of the components. Enclosures can be bayed to the front and rear, as well as to the sides.

Load capacity: up to 500 kg.

Base:

Open base frame, without gland plates, for optional individual configuration with base modules from the range of accessories.

Front and rear door:

Glazed sheet steel door at the front, with 3 mm single-pane safety glass (ESG).

One-piece solid sheet steel door at the rear. Both with two hinges.

Front and rear door with design handle and 2-point locking rod, security lock 3524 E, exchangeable for an AX comfort handle for optional integration of a profile half-cylinder. Door hinge side can be swapped, door opening angle 135° for stand-alone enclosures, 105° with baying. Door hinges with captive hinge pins.

Roof plate:

Multi-piece solid roof plate, comprising a welded centre piece and cable guide struts integrated without the need for tools at the outside.

With openings for cable entry over the full enclosure depth on both sides.

Roof plate centre piece and cable guide struts with rounded edges for

system-compliant cable entry taking into account the minimum bending radius.

Roof incl. concealed cut-out to accommodate a fan unit for active ventilation.

For convenient cable entry, the cable guide struts can simply be removed without the need for tools and then clipped back into place when finished. The integrated bending radius avoids cable routing over sharp edges.

Cable entry options can be expanded with brush strips from the range of accessories.

Mounting levels:

Enclosure pre-configured with two 482.6 mm (19") mounting levels, front and rear.

The total static load capacity of both mounting levels is 500 kg.

Mounting levels comprising universal mounting angles, front and rear, depth-variable, 15 mm pitch pattern, screwed to depth stays of the enclosure frame at top and bottom.

Imperial mounting levels can be positioned either symmetrically or asymmetrically with an offset to each other. Alternative mounting dimensions for 21", 23" or 24" components can also be realised.

Mounting angles front and rear, material thickness 2.0 mm, with additional pitch pattern in accordance with the standard EIA 310 E. All height units are marked on the mounting angles and numbered in opposite directions. Height unit markings on both mounting levels can be read from both inside and outside for simplified component installation.

Front mounting angles prepared for tool-free mounting of cable routing aids and organisation of structured cabling with maximum packing density.

Rear mounting angles prepared on both sides for mounting of a Power Distribution Unit (PDU) in 1 U form factor for electrical power distribution in the enclosure, avoids occupying component installation space thanks to space-saving side mounting in the zero-U space between mounting level and side panel.

Side panels:

One-piece lockable side panels with integrated security lock 3524 E mounted on the enclosure.

Material:

Enclosure frame, roof: Sheet steel, 1.5 mm

Rear door: Sheet steel, 1.2 mm

Front door: Sheet steel, 1.2 mm; single-pane safety glass (ESG) 3.0 mm

19" mounting angles: Sheet steel, 2.0 mm

Surface:

Panel parts and doors powder-coated in RAL 7035

Interior installations dipcoat-primed in RAL 9005

Approvals:

CE Declaration of Conformity

RoHS 3

Dimensions (WHD): 800x2000x1000 mm

Model no.: 7888.200

Manufacturer: Rittal GmbH & Co. KG