

Rittal – The System.

Faster – better – everywhere.



AS 4050.452 Crimping machine L8

State: 19/10/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.452 - Crimping machine L8

Electro-pneumatically powered wire stripping and crimping machine for loose, insulated wire end ferrules.

Features

| | |
|---------------------------|--|
| Model No. | AS 4050.452 |
| Design | Touchscreen display |
| Product description | Electro-pneumatically driven wire stripping and crimping centre for loose, insulated wire end ferrules. |
| Benefits | Easy to operate Secure, fast processing of insulated wire end ferrules No set-up time, thanks to automatic tool change Handling of special wires supported Simple, quick component mounting Automatic detection of cross-sections |
| Technical specifications | Crimping range 0.5 - 2.5 mm ² (AWG 20 - 14) Crimping length 8 mm (0.31 in.) Insertion length 35 mm (1.38 in.) Processing of wire end ferrules with plastic collars in special sizes supported |
| Supply includes | Crimping machine L8 1 vibratory bowl feeder 0.5 - 1.5 mm ² 1 vibratory bowl feeder 1.5 - 2.5 mm ² |
| Note | The standard crimping form is trapezoid – others available on request |
| Dimensions | Width: 390 mm Height: 460 mm Depth: 330 mm |
| Compressed air connection | 5.5 bar |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Apparent power | 110 VA |
| Compression | Trapezoid crimp |

Features

| | |
|-----------------------|---------------|
| Cycle time | 1.5 s |
| Packs of | 1 pc(s). |
| Weight/pack | 31 kg |
| Net weight | 34.6 |
| Gross weight | 34.67 |
| Customs tariff number | 84798997 |
| EAN | 4028177804869 |
| ETIM 8 | EC002778 |
| ETIM 7.0 | EC002778 |
| ECLASS 8.0 | 36600890 |