

**Rittal – The System.**

Faster – better – everywhere.



**DK 7000.630**

**Socket strip in a plastic housing**

State: 19/10/2024 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7000.630 - Socket strip in a plastic housing

Socket strips 230 V, unrestricted use, including angular connectors, thanks to the long row arrangement of plug-type contacts.

## Features

Model No.	DK 7000.630
Product description	8-way socket strip for earthing-pin plug (type F, CEE 7/4) The strip may be mounted vertically on the enclosure frame or in the rear 482.6 mm (19") section. In the 482.6 mm (19") section, more than 2 U of space is required. The sockets are arranged at an angle of 45° so that angular connectors are also easily used. The connection cable is contacted in a terminal slot in the strip. The terminal slot has a separate cover and external terminals for separate earthing.
Material	Plastic
Supply includes	Connection cable Assembly screws 2 serrated washers Captive nuts M6, conductive Nuts
Design	Without switch
Sockets	8 x D, earthing-pin (type F, CEE 7/3)
Length of connection cable	2 m
Connection cable (type)	H05VV-F3G1.5 with wire end ferrules
Rated operating voltage	230 V AC, 50 Hz
Rated voltage	230 V AC, 50 Hz
Rated current (max.)	16 A
Type of electrical connection	Wire end ferrules
Installation options	TE 7000, rear 482.6 mm (19") section (> 2 U) TE 7000, vertically mounted on the frame
Colour of socket	Black
Packs of	1 pc(s).

# Features

---

Weight/pack	0.92 kg
Net weight	0.92
Gross weight	1.026
Customs tariff number	85366990
EAN	4028177438569
ETIM 7.0	EC000330
ECLASS 8.0	27142604

# Approvals

---

Explanations

Declaration of conformity

# Tender text

Socket strip, 8-way, earthing pin  
8-way socket strip for earthing-pin plug/version D.  
The strip is made of plastic and may be mounted vertically on the TE frame or in the rear 482.6 mm (19 inch) section, more than 2 U of space is required. The sockets are arranged at an angle of 45° so that angular connectors are also easily used.