

**Rittal – The System.**

Faster – better – everywhere.



# HD 2410.131 Cable gland HD

State: 27/09/2024 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 2410.131 - Cable gland HD

More compact design and the lock nut is included with the supply.



## Features

Model No.	HD 2410.131
Design	EMC
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M25 x 1.5
For cable diameters	12 - 17 mm
Operating temperature range	-20 °C...100 °C

# Features

---

IP protection category to IEC 60529	IP69 / IPX8 (5 bar, 30 min)
Packs of	5 pc(s).
Weight/pack	0.885 kg
Net weight	0.54
Gross weight	0.59
Customs tariff number	73181900
EAN	4028177928664
ETIM 8	EC000441
ETIM 7.0	EC000441
ECLASS 8.0	27149109

# Approvals

---

Approvals	UL + C-UL (listed) VDE
-----------	---------------------------