

Rittal – The System.

Faster – better – everywhere.



SV 9344.130

NH fuse-switch-disconnectors, size 00 to 3

State: 19/10/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.130 - NH fuse-switch-disconnectors, size 00 to 3 with electronic fuse monitoring

Features

Model No.	SV 9344.130
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 32 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	250 A
For NH size	1
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm
Connection for round conductor cross-sections	10 - 150 mm ²
Rated operating voltage	400 V - 690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	2.34 kg
Net weight	2.3

Features

Gross weight	2.343
Copper weight (kg per piece)	0.3
Customs tariff number	85365080
EAN	4028177540620
ETIM 7.0	EC001040
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK