


Rittal – The System.

Faster – better – everywhere.



SV 9677.920 Connection block

State: 26/09/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.920 - Connection block

For connecting cables and laminated copper bars.

Features

Model No.	SV 9677.920
Product description	For connecting cables and laminated copper bars.
Material	Sheet steel, zinc-plated E-Cu, tin-plated
Cable outlet	Top/bottom
Type of electrical connection	Ring terminal M12
Rated current max.	1,600 A
Dimensions	Width: 98 mm
Connection for round conductor cross-sections	240 mm ²
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Weight/pack	1.66 kg
Net weight	1.6
Gross weight	1.662
Copper weight (kg per piece)	1.471
PCF/PU (Cradle-to-Gate)	6.3 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	85369095
EAN	4028177806351
ETIM 7.0	EC001900
ECLASS 8.0	27400613

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK