

Rittal – The System.

Faster – better – everywhere.



TS 8609.260 Divider panel

State: 19/10/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8609.260 - Divider panel for TS

For shielding individual enclosure cells. Thanks to the symmetry of the frame system, the divider panel can also be used at the rear.



Features

Model No.	TS 8609.260
Product description	For shielding individual enclosure cells. All-round, double fold for stability and to hold the seal. Thanks to the symmetry of the enclosure frame, divider panels may also be fitted at the rear, dimensions permitting.
Applications	Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.
Material	Sheet steel, 1.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
To fit	Enclosure type: TS 8 Height: = 2,200 mm Depth: = 600 mm
Installation options	For mounting on the outer mounting level This leaves the inner level free for further population
Assembly instruction	The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/finished off with a cover.

Features

IP protection category to IEC 60529	IP 54
-------------------------------------	-------

Packs of	1 pc(s).
----------	----------

Weight/pack	15.6 kg
-------------	---------

Net weight	14.176
------------	--------

Gross weight	14.922
--------------	--------

Customs tariff number	94039910
-----------------------	----------

EAN	4028177208773
-----	---------------

ETIM 7.0	EC002525
----------	----------

ECLASS 8.0	27182102
------------	----------
