

Rittal – The System.

Faster – better – everywhere.



VX 8840.130

Bayed enclosure system VX25

State: 26/09/2024 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8840.130 - Bayed enclosure system VX25 Basic enclosure with glazed door

The VX basic enclosure with glazed door for industrial applications: Enclosure frame with glazed door at the front, rear door, roof plate, divided gland plates. Perfectly suited to efficient enclosure interior installation.

Features

| | |
|-----------------------------------|---|
| Model No. | VX 8840.130 |
| Material | Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Glazed door: Single-pane safety glass, 3 mm Rear door: Sheet steel, 2.0 mm Gland plates: Sheet steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Glazed aluminium door at the front (180°) Sheet steel door at the rear (130°) Lock front and rear: 3 mm double-bit Roof plate Gland plate |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 800 mm |
| Protection category to IEC 60 529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Type rating to UL 50E | Type 1 Type 12 |
| IK Code | IK08 |

Features

| | |
|----------------|---------------|
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Weight/pack | 75.4 kg |
| EAN | 4028177951396 |
| ETIM 7.0 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Certificates | Surface finish Protection category |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

Schaltschrank (Anreih-System) Basic Enclosure with Glazed door

Housing:

symmetrical frame construction, consisting of closed an profiled hollow section with 25 mm pitch pattern.

Frame with integrated blind rivet nut M6 enables for protection class oriented fixing of fitting parts at the profile.

All sections have chamfered edges.

Horizontal sections have a protection lip above the seal.

Circumferential equal profiles with two mounting levels accessible from inside and outside of the frame for space-saving and fast interior installation.

The entire square perforation enables the use of cage nuts and metrical screws up to M8.

Welded base frame with integrated base reinforcement allows to fasten the enclosure on the underground through the inner side of the enclosure.

Mounted three-piece gland plate, removable and exchangeable.

Bayable on all sides.

Load capacity up to 15.000 N.

Aluminum glazed door front:

with foamed-in seal,

4-point latch locking rod, double-bit insert to DIN 43668,

Door hinge may be swapped from right to left.

Hinges with captive hinge pins,

door opening angle 180°.

Sheet steel door rear:

with foamed-in seal, with removable tubular door frame

with holes on a 25 mm pitch pattern and

integrated cable clamping.

4-point latch locking rod, double-bit insert to DIN 43668,

Door hinge may be swapped from right to left.

Hinges with captive hinge pins, door opening angle 130°

tool-less retrofittable to 180°.

Roof Plate:

With foamed-in seal,

screw-fastened and removable.

Roof with roof fastening screws M12.

Flat parts:

Roof, aluminum glazed door front, sheet steel door rear,

gland plaets included in scope of supply.

Side panels are available as separate accessory.

Rear door, roof and gland plates are electrically

conductive connected with the frame

(automatic potential equalisation) to DIN 62 208 and

prepared for the additional attachment of earthing straps.

QR Code:

Printed QR Code on roof, rear door and type plate

and type plate for unambiguous marking and for

easy recall of relevant product information and

documentation, as well as clear traceability of

single parts.

Material:

Enclosure frame, rear panel and roof: 1.5 mm sheet steel

Glazed door: single-pane safety glass: 3 mm, aluminum

Rear door: 2 mm, sheet steel

Gland plates: 1,5 mm, sheet steel, zinc-plated

Surface Finish:

Triple surface treatment ensures optimum protection

against corrosion and is resistant to mineral oils,

lubricants, machining emulsions and solvents:

nanoceramic coating, electro-phoretic dipcoat-priming,

textured powder coating in RAL 7035 for outside surfaces.

Glazed door from aluminum.

Protection category to IEC 60 529

(with mounted side panels): IP 55

Protection category to UL 508A: Type 1, 12

Impact protection to IEC 62 262: IK08

Dimensions (W x H x D): 600x2000x800 mm