

Rittal – The System.

Faster – better – everywhere.



SK 3239.100 TopTherm Filter Fan Units

State: 7/8/2024 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.100 - TopTherm Filter Fan Units

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.



Features

Model No.	SK 3239.100
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Color	RAL 7035
Supply includes	Complete unit ready to install, including fleece filter mat
Fan	Axial, shaded pole motor
Unimpeded air flow (with fleece filter)	At 50 Hz: 100 m ³ /h At 60 Hz: 115 m ³ /h At 50 Hz: 58.9 cfm At 60 Hz: 67.7 cfm
Unimpeded air flow (with folded filter)	At 50 Hz: 110 m ³ /h At 60 Hz: 125 m ³ /h At 50 Hz: 64.74 cfm At 60 Hz: 73.57 cfm
Air throughput with outlet filter incl. fleece filter mat (quantity x order number)	1 x 3239200: 74/87 m ³ /h 2 x 3239200: 84/98 m ³ /h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz

Features

Rated power Pel	At 50 Hz: 16.5 W At 60 Hz: 14 W
Rated current max.	At 50 Hz: 0.12 A At 60 Hz: 0.09 A
Dimensions	Width: 204 mm Height: 204 mm Width: 8.03 " Height: 8.03 "
Installation depth	90 mm 3.54 "
Mounting cut-out	Width of opening: 177 mm Cut-out height: 177 mm Width of opening: 6.97 " Cut-out height: 6.97 "
Protection category IP to IEC 60529	IP54 with fleece filter/folded filter IP55 with folded filter and absorber mat IP56 with fleece filter/folded filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter/folded filter Type 3, 3R, 4, 4X with fleece filter/folded filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	A folded filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For the 3237.XXX filter fan, the electrical connection is made via 2 individual wires (length approx. 300 mm) on the unit, for all other filter fans, it's made via a spring-loaded terminal
Service life of fans (L10, 40 °C))	At 50 Hz: 68,200 h At 60 Hz: 68,200 h
Operating temperature range	-15 °C...55 °C 5 °F...131 °F
Storage temperature range	-30 °C...70 °C -22 °F...158 °F
Noise pressure level	At 50 Hz: 46 dB(A) At 60 Hz: 49 dB(A)

Features

Weight/packaging unit	1.04 kg 2.3 lb.
Packaging unit	1 pc(s).
Customs tariff number	84145915
EAN	4028177651814
E-Number Sweden	E3404340
ETIM 8	EC000320
ETIM 7.0	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK